

RP73PF2A1K4BTDF

✓ ACTIVE

Holsworthy | Holsworthy RP73

TE Internal #: 3-2176092-0

1.4K ohm, Surface Mount Precision Resistor, Thin Film, 0805, .25 W, .1 %, ±25 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height, Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistance Value: 1.4K  $\Omega$

Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 0805

Power Rating: .25 W

Features

Product Type Features

|                   |                    |
|-------------------|--------------------|
| Resistor Type     | Precision Resistor |
| Element Type      | Thin Film          |
| Package Size Code | 0805               |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

|                             |                           |
|-----------------------------|---------------------------|
| Operating Voltage           | 150 V                     |
| Resistance Value            | 1.4K $\Omega$             |
| Power Rating                | .25 W                     |
| Resistance Class            | 1k $\Omega$ – 1M $\Omega$ |
| Passive Component Tolerance | .1 %                      |

Termination Features

|                                         |        |
|-----------------------------------------|--------|
| Surface Mount Resistor Termination Type | Solder |
| Number of Terminations                  | 2      |

Dimensions

|                |                 |
|----------------|-----------------|
| Product Height | .55 mm[.022 in] |
| Product Length | 2 mm[.079 in]   |



|               |                  |
|---------------|------------------|
| Product Width | 1.25 mm[.049 in] |
|---------------|------------------|

Usage Conditions

|                         |            |
|-------------------------|------------|
| Temperature Coefficient | ±25 ppm/°C |
|-------------------------|------------|

Industry Standards

|                            |   |
|----------------------------|---|
| Moisture Sensitivity Level | 1 |
|----------------------------|---|

Packaging Features

|                  |                |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RP73PF2A1K4BTDF

1.4K ohm, Surface Mount Precision Resistor, Thin Film, 0805, .25 W, .1 %, ±25 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height, Holsworthy RP73



TE Part # 2-2176308-7  
RP 1E 0.1W 249K 0.1% 25PPM 5K RL

TE Part # 1625867-2  
RP 1J 0.166W 10K 0.1% 25PPM 1K RL

TE Part # 2176308-5  
RP 1E 0.1W 147K 0.1% 25PPM 5K RL

TE Part # 2176093-5  
RP 2A 0.25W 10K 0.1% 25PPM 1K RL

TE Part # 1-2176092-8  
RP 2A 0.25W 1K0 0.1% 25PPM 1K RL

Also in the Series | [Holsworthy RP73](#)

[Surface Mount Resistors\(4227\)](#)

Customers Also Bought

TE Part #4-2213767-7  
AV19 DPM 3A MOVE RING LED RED 24V

TE Part #6339082-3  
LED STK MJ ASSY,2X4,8 POS,CAT5

TE Part #1-2176238-7  
CPF A 0805 75R 0.1% 25PPM 5K RL

TE Part #828548-2  
2P AMP QUICK STLEI



TE Part #214355-E  
MSPEED 133 M SMD M1 \* A-G VVV 137 176 \*

TE Part #5-2213767-5  
AV19 DPM 3A MOVE RING LED GREEN 24V

TE Part #5-1614893-9  
CPF 0805 54K9 0.1% 25PPM 1K RL

TE Part #5-2176363-0  
RQ 0402 1K4 0.1% 10PPM 5K RL





Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-2176092-0\_BA.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-2176092-0\_BA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-2176092-0\_BA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RP73-0915

English