

Technical Information: Alkaline Manganese Batteries

LR03LP

■ Appearance



The data in this document are for descriptive purpose only and are not intended to make or imply any guarantee or warranty

■ Technical data & Discharging time

Type designation	LR03LP		
Nominal voltage	1.5V		
Weight	10g		
Outer dimension	Height	44.2mm	
	Diameter	10.3mm	
Typical duration @20°C	5.1Ω 4min ON/56min OFF 8h/day (0.9V)	Portable Lighting	230min
	5.1Ω 1h/day (0.8V)	Toy	220min
	24Ω 15s ON/45s OFF 8h/day (1.0V)	Remote Control	19h
	50mA 1h ON /11h OFF Repeat (0.9V)	Digital Audio	20h

Note) Value in parentheses is end point voltage of each discharge.

■ Typical discharging curve

