


2183

Max. 24 W

AC/DC DESKTOP REGULATED

- Max. 24 W output power
- 230 VAC input voltage
- Available with EU or UK terminals
- Compliance with relevant worldwide safety standards
- Exchangeable output plugs, providing:
 - reduced stocking requirements
 - short delivery lead times
 - snap-locks for added safety



<u>Technical specifications</u>	
<i>Input voltage:</i>	230 VAC, 50 Hz
<i>Output voltage:</i>	24 VDC
<i>Max.output power:</i>	24 W
<i>Load current:</i>	1 A
<i>Temperature range:</i>	-10°C to +40°C
<i>Protection:</i>	Protected against internal short circuit by thermal fuse in primary
<i>Insulation class</i>	II
<i>Electrical safety</i>	EN 60950
<i>EMC, Emission</i>	EN 61000-6-3
<i>EMC, Immunity</i>	EN 61000-6-1
<i>Mains connections:</i>	EU or UK
<i>Output terminals:</i>	Secondary cable w/snap-on plugs
<i>Dimensions:</i>	129x78x58mm
<i>Weight:</i>	1,2 kg

19062006

www.mascot.no
sales@mascot.no

Phone:
Fax:

Main Office
PO Box 177
N-1601 FREDRIKSTAD
NORWAY
+47 69 36 43 00
+47 69 36 43 01

Mascot UK
Box 2090, Salisbury
Wiltshire SP2 2BH
UK
+44 1722 504 853
+44 845 299 1210

Mascot DE-AT-CH-BENELUX
Hirschbergstr. 28/7
D-74838 LIMBACH
GERMANY
+49 6287 95140
+49 6287 95141

Mascot DE-AT-CH-BENELUX
Tettlinger Str. 52
D-88239 WANGEN
GERMANY
+49 7528 951677
+49 7528 951678

Mascot France
38 rue Leo Lagrange
94270 Le Kremlin Bicêtre
FRANCE
+33 1 46 58 71 85
+33 1 46 58 71 85