

## Dual-Bay SATA HDD Docking Station for 2 x 2.5/3.5" SATA SSDs/HDDs - USB 3.0

Product ID: SDOCK2U33V



This dual-bay SATA HDD/SSD docking station lets you dock and swap drives from your desktop or laptop computer simultaneously, using a single USB port. It supports two 2.5/3.5" SATA hard drives or solid-state drives.

### Transfer files quickly

The dual-bay docking station supports USB 3.0, also known as USB 3.1 Gen 1, providing fast data transfer speeds of up to 5Gbps. It also supports UASP, for enhanced performance.

Ideal for IT professionals, such as system administrators and technicians, the hard drive dock enables you to complete device-management tasks more efficiently, such as disk image duplication, data recovery, backing up and archiving hard drives, and transferring content between drives and devices. It also enhances your workflow, by providing quick access to your hard drives, with the ability to easily swap drives in and out as needed.

## **Easy drive access**

Designed for easy drive access, the hard drive dock enhances your workflow, by providing quick access to two hard drives, with the ability to easily swap drives in and out as needed. The hard drive dock features a convenient top-loading design with independent drive doors that make it easy to add or remove drives.

## **Get up and running quickly**

The dual-bay SATA HDD/SSD docking station is OS independent, with no drivers or software installation required, for easy setup.

The SDOCK2U33V is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Ideal for system builders and other IT specialists who need quick access to drives for imaging
- Backup data quickly to an external drive for archiving
- Transfer data from one hard drive to another
- Backup important data and easily take the drive to an offsite location for safekeeping

### Features

- Access two 2.5/3.5" SATA hard drives (HDD) or solid state drives (SSD) simultaneously and hot swap drives in and out
- USB 3.0 with data transfer speeds of up to 5Gbps
- Convenient top-loading design with independent drive doors
- Plug-and-play functionality
- Easy to set up with no driver or software installation required

<b>Hardware</b>	Warranty	2 Years
	Bus Type	USB 3.0
	Chipset ID	ASMedia - ASM1153E
	Compatible Drive Types	SATA
	Drive Installation	Removable
	Drive Size	2.5in & 3.5in
	Fan(s)	No
	Interface	USB 3.0
	Number of Drives	2
<b>Performance</b>	4Kn Support	Yes
	Max Drive Capacity	Currently tested with hard drives up to 10TB at 7200 RPM
	Port Multiplier	No
	RAID	No
	S.M.A.R.T. Support	Yes
	TRIM Support	Yes
	Type and Rate	USB 3.0 - 5 Gbit/s SATA III (6 Gbps)
	UASP Support	Yes
<b>Connector(s)</b>	Drive Connectors	2 - SATA Data & Power Combo (7+15 pin) Receptacle
	Host Connectors	1 - USB 3.1 USB Type-B (9 pin, Gen 1, 5 Gbps) Female Output
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Indicators</b>	LED Indicators	2 - drive activity LED 1 - power LED
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	1.5 A
	Input Voltage	100 - 240 AC
	Output Current	3 A
	Output Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	36
	Power Source	AC Adapter Included

<b>Environmental</b>	Humidity	20%RH~80%RH
	Operating Temperature	5°C to 35°C (41°F to 95°F)
	Storage Temperature	-20°C to 50°C (-4°F to 122°F)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Aluminum and Plastic
	Product Height	6.2 cm [2.4 in]
	Product Length	11.4 cm [4.5 in]
	Product Width	13 cm [5.1 in]
	Weight of Product	370 g [13.1 oz]
<b>Packaging Information</b>	Package Height	12 cm [4.7 in]
	Package Length	13.5 cm [5.3 in]
	Package Width	12.5 cm [4.9 in]
	Shipping (Package) Weight	0.8 kg [1.7 lb]
<b>What's in the Box</b>	Included in Package	1 - drive docking station
		1 - 1.2 m USB 3.0 cable
		1 - universal power adapter (NA/JP, UK, EU, ANZ)
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.