

LONG LIFE DRILLING REINFORCED CONCRETE

EXPERT SDS plus-7X Hammer Drill Bit

EXPERT

- ① Exceptionally durable drill bit tip with Bosch Carbide Technology
- ② Punch through reinforced concrete with a 4-cutter full carbide head
- ③ Highly resistant drill tip connection thanks to Bosch's special welding process



* vs. Bosch SDS plus-3



Video



BOSCH

EXPERT SDS PLUS-7X HAMMER DRILL BIT



- ▶ Ideal for drilling holes in reinforced concrete, e.g. to anchor interior installations such as air conditioning, heating pipes, electrical wiring and lights
- ▶ Best for electricians: long lasting and powerful
- ▶ Lasts up to 3x longer than Bosch SDS plus-3 Drill Bit
- ▶ Fits all SDS plus rotary hammer drills



PRODUCT PROPERTIES				ORDERING INFORMATION				
	Diameter (D) mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number
Pack of 1								
	3.50	50	115	P1e	1	1	531 281	2 608 900 055
	3.50	100	165	P1e	1	1	531 298	2 608 900 056
	4.00	50	115	P1e	1	1	531 304	2 608 900 057
	4.00	100	165	P1e	1	1	531 311	2 608 900 058
	5.00	50	115	P1e	1	5	531 328	2 608 900 059
	5.00	100	165	P1e	1	5	531 335	2 608 900 060
	5.00	150	215	P1e	1	5	531 342	2 608 900 061
	5.00	200	265	P1e	1	5	531 359	2 608 900 062
	5.00	250	315	P1e	1	5	531 366	2 608 900 063
	5.00	400	465	P1e	1	1	531 373	2 608 900 064
	5.50	50	115	P1e	1	5	531 380	2 608 900 065
	5.50	100	165	P1e	1	5	531 397	2 608 900 066
	5.50	150	215	P1e	1	5	531 403	2 608 900 067
	5.50	200	265	P1e	1	5	531 410	2 608 900 068
	5.50	250	315	P1e	1	1	531 427	2 608 900 069
	5.50	400	465	P1e	1	1	531 434	2 608 900 070
	6.00	50	115	P1e	1	5	531 441	2 608 900 071
	6.00	100	165	P1e	1	5	531 458	2 608 900 072
	6.00	150	215	P1e	1	5	531 465	2 608 900 073
	6.00	200	265	P1e	1	5	531 472	2 608 900 074
	6.00	250	315	P1e	1	5	531 489	2 608 900 075
	6.00	400	465	P1e	1	1	531 496	2 608 900 076
	6.50	50	115	P1e	1	1	531 502	2 608 900 077
	6.50	100	165	P1e	1	5	531 519	2 608 900 078
	6.50	150	215	P1e	1	5	531 526	2 608 900 079
	6.50	200	265	P1e	1	5	531 533	2 608 900 080
	6.50	250	315	P1e	1	1	531 540	2 608 900 081
	6.50	400	465	P1e	1	1	531 557	2 608 900 082
	7.00	50	115	P1e	1	1	531 564	2 608 900 083
	7.00	100	165	P1e	1	1	531 571	2 608 900 084
	7.00	150	215	P1e	1	1	531 588	2 608 900 085
	7.00	200	265	P1e	1	1	531 595	2 608 900 086
	8.00	50	115	P1e	1	5	531 601	2 608 900 087
	8.00	100	165	P1e	1	5	531 618	2 608 900 088
	8.00	150	215	P1e	1	5	531 625	2 608 900 089
	8.00	200	265	P1e	1	5	531 632	2 608 900 090
	8.00	250	315	P1e	1	1	531 649	2 608 900 091



BOSCH

EXPERT SDS PLUS-7X HAMMER DRILL BIT

PRODUCT PROPERTIES				ORDERING INFORMATION					
Diameter (D) mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number		
8.00	300	365	P1e	1	5	531 656	2 608 900 092		
8.00	400	465	P1e	1	1	531 663	2 608 900 093		
9.00	100	165	P1e	1	1	531 670	2 608 900 094		
9.00	150	215	P1e	1	1	531 687	2 608 900 095		
10.00	50	115	P1e	1	1	531 694	2 608 900 096		
10.00	100	165	P1e	1	5	531 700	2 608 900 097		
10.00	150	215	P1e	1	5	531 717	2 608 900 098		
10.00	200	265	P1e	1	5	531 724	2 608 900 099		
10.00	250	315	P1e	1	1	531 731	2 608 900 100		
10.00	300	365	P1e	1	5	531 748	2 608 900 101		
10.00	400	465	P1e	1	1	531 755	2 608 900 102		
10.00	550	600	P1e	1	1	531 762	2 608 900 103		
10.00	950	1000	P1e	1	1	531 779	2 608 900 104		
11.00	100	165	P1e	1	1	531 786	2 608 900 105		
11.00	150	215	P1e	1	1	531 793	2 608 900 106		
11.00	200	265	P1e	1	1	531 809	2 608 900 107		
12.00	100	165	P1e	1	5	531 816	2 608 900 108		
12.00	150	215	P1e	1	5	531 823	2 608 900 109		
12.00	200	265	P1e	1	5	531 830	2 608 900 110		
12.00	250	315	P1e	1	5	531 847	2 608 900 111		
12.00	300	365	P1e	1	5	531 854	2 608 900 112		
12.00	400	465	P1e	1	1	531 861	2 608 900 113		
12.00	550	600	P1e	1	1	531 878	2 608 900 114		
12.00	950	1000	P1e	1	1	531 885	2 608 900 115		
13.00	100	165	P1e	1	1	531 892	2 608 900 116		
13.00	150	215	P1e	1	1	531 908	2 608 900 117		
13.00	200	265	P1e	1	1	531 915	2 608 900 118		
14.00	100	165	P1e	1	5	531 922	2 608 900 119		
14.00	150	215	P1e	1	5	531 939	2 608 900 120		
14.00	200	265	P1e	1	5	531 946	2 608 900 121		
14.00	250	315	P1e	1	5	531 953	2 608 900 122		
14.00	300	365	P1e	1	1	531 960	2 608 900 123		
14.00	400	465	P1e	1	1	531 977	2 608 900 124		
14.00	550	600	P1e	1	1	531 984	2 608 900 125		
14.00	950	1000	P1e	1	1	531 991	2 608 900 126		
15.00	100	165	P1e	1	1	532 004	2 608 900 127		
15.00	200	265	P1e	1	1	532 011	2 608 900 128		
15.00	400	465	P1e	1	1	532 028	2 608 900 129		
16.00	150	215	P1e	1	5	532 035	2 608 900 130		
16.00	200	265	P1e	1	5	532 042	2 608 900 131		
16.00	250	315	P1e	1	1	532 059	2 608 900 132		
16.00	400	465	P1e	1	1	532 066	2 608 900 133		
16.00	550	600	P1e	1	1	532 073	2 608 900 134		
16.00	950	1000	P1e	1	1	532 080	2 608 900 135		
17.00	150	215	P1e	1	1	532 097	2 608 900 136		
17.00	250	315	P1e	1	1	532 103	2 608 900 137		
18.00	200	250	P1e	1	1	532 110	2 608 900 138		
18.00	400	450	P1e	1	1	532 127	2 608 900 139		
18.00	550	600	P1e	1	1	532 134	2 608 900 140		
18.00	950	1000	P1e	1	1	532 141	2 608 900 141		
20.00	200	250	P1e	1	1	532 158	2 608 900 142		
20.00	400	450	P1e	1	1	532 165	2 608 900 143		



BOSCH

EXPERT SDS PLUS-7X HAMMER DRILL BIT

PRODUCT PROPERTIES			ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number
20.00	550	600	P1e	1	1	532 172	2 608 900 144
20.00	950	1000	P1e	1	1	532 189	2 608 900 145
22.00	200	250	P1e	1	1	532 196	2 608 900 146
22.00	400	450	P1e	1	1	532 202	2 608 900 147
22.00	550	600	P1e	1	1	532 219	2 608 900 148
22.00	950	1000	P1e	1	1	532 226	2 608 900 149
24.00	400	450	P1e	1	1	532 233	2 608 900 150
25.00	400	450	P1e	1	1	532 240	2 608 900 151
25.00	550	600	P1e	1	1	532 257	2 608 900 152
25.00	950	1000	P1e	1	1	532 264	2 608 900 153
28.00	400	450	P1e	1	1	532 271	2 608 900 154
30.00	400	450	P1e	1	1	532 288	2 608 900 155
Pack of 10							
4.00	50	115	P1h	10	1	532 295	2 608 900 156
5.00	50	115	P1h	10	1	532 301	2 608 900 157
5.00	100	165	P1h	10	1	532 318	2 608 900 158
6.00	50	115	P1h	10	1	532 325	2 608 900 159
6.00	100	165	P1h	10	1	532 332	2 608 900 160
6.00	150	215	P1h	10	1	532 349	2 608 900 161
6.00	200	265	P1h	10	1	532 356	2 608 900 162
6.50	100	165	P1h	10	1	532 363	2 608 900 163
6.50	150	215	P1h	10	1	532 370	2 608 900 164
6.50	200	265	P1h	10	1	532 387	2 608 900 165
7.00	100	165	P1h	10	1	532 394	2 608 900 166
8.00	100	165	P1h	10	1	532 400	2 608 900 167
8.00	150	215	P1h	10	1	532 417	2 608 900 168
8.00	200	265	P1h	10	1	532 424	2 608 900 169
10.00	100	165	P1h	10	1	532 431	2 608 900 170
10.00	150	215	P1h	10	1	532 448	2 608 900 171
10.00	200	265	P1h	10	1	532 455	2 608 900 172
12.00	100	165	P1h	10	1	532 462	2 608 900 173
12.00	150	215	P1h	10	1	532 479	2 608 900 174
12.00	200	265	P1h	10	1	532 486	2 608 900 175
14.00	200	265	P1h	10	1	532 493	2 608 900 176
16.00	200	265	P1h	10	1	532 509	2 608 900 177
Pack of 30							
5.00	50	115	P0h	30	1	532 516	2 608 900 178
5.00	100	165	P0h	30	1	532 523	2 608 900 179
6.00	50	115	P0h	30	1	532 530	2 608 900 180
6.00	100	165	P0h	30	1	532 547	2 608 900 181
6.00	150	215	P0h	30	1	532 554	2 608 900 182
8.00	100	165	P0h	30	1	532 561	2 608 900 183
8.00	150	215	P0h	30	1	532 578	2 608 900 184
8.00	200	265	P0h	30	1	532 585	2 608 900 185
10.00	100	165	P0h	30	1	532 592	2 608 900 186
10.00	150	215	P0h	30	1	532 608	2 608 900 187
10.00	200	265	P0h	30	1	532 615	2 608 900 188
12.00	150	215	P0h	30	1	532 622	2 608 900 189
12.00	200	265	P0h	30	1	532 639	2 608 900 190
Pack of 50							
6.00	100	165	P0h	50	1	532 646	2 608 900 191



BOSCH

EXPERT SDS PLUS-7X HAMMER DRILL BIT

PRODUCT PROPERTIES				ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number	
8.00	100	165	P0h	50	1	532 653	2 608 900 192	
10.00	100	165	P0h	50	1	532 660	2 608 900 193	
10.00	150	215	P0h	50	1	532 677	2 608 900 194	



BOSCH