



Cable and Fibre Type

Grade of the cable: LSZH

Fibre type (ISO/IEC 11801-2002)		Outer Sheath Colour
62.5/125	OM1	Orange
50/125	OM2	Orange
50/125	OM3	Purple
09/125	OS1	Yellow

Optical Performance (IEC 61300-3-4):

Multimode (@ 1300nm)

Max. IL - 0.30dB Typical: 0.20dB

Singlemode: (@1310nm and/or 1550nm)

Max. IL - 0.30dB Typical: 0.20dB Return Loss: >50dB

RoHS Compliant

Coiling Diameter: Coiling Diameter of the patchcord shall be greater than 200mm

Packing: Each product shall be individually bagged and identified with a unique number printed on an ID label affixed to the product. Also, each product will be supplied with a Test Certificate.

Id No.	Description	Ea
1.	ST Connector	4
2.	ST Boots	4
3.	Identification Label	1
4.	2.8mm Duplex Cable (L m)	1
5.	Black Tape	2



REV	DESCRIPTION	DATE	DRN	APD	REV	DESCRIPTION (REVISION RECORD)	DATE	DRN	APD
MATERIAL		SIZE	TITLE		DGN				
FINISH		A4	ST-ST Duplex PATCHCORD		DRN				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PART NO.		DWC/REF NO.		CHD			
SCALE		REV		SHEET		QA			
Not to Scale		01		1 OF 1		VER			
ALL DIMENSIONS IN MM		APD		SIGNATURE		DATE			
ANGLES		± ANG							