

FEATURES

- Body zinc plated steel
- Plunger stainless steel
- Lifting ring stainless steel
- Thread size M6 to M12
- Comes as standard with lift ring and locking nut

RS PRO M10 Index Plunger

RS Stock No.: 237-687



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Ball & Spring Plungers



Product Description ATTRIBUTE 1

These Basic Indexing Plungers with pull/lift ring from our own RS PRO brand are designed with simple finish with very small dimensions.

General Specifications

Туре	Index Plunger	
Body Material	Body – zinc plated steel, Plunger – stainless steel, Lifting ring – stainless steel	
Thread Size	M10	
Applications	Designed for applications where high precisions indexing is not required	

Mechanical Specifications


Ball Diameter	6mm
Length	20mm

Approvals

Compliance/Certifications	RoHS

Ball & Spring Plungers





Part No.	Α	В	С	Thread size	Plunger diameter (mm)
237671	14	12	4	M6	4
237750	18	16	5	M8	5
237687	24	20	6	M10	6
237564	30	24	8	M12	8