



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # 2176322-8
[SMV 1W 390K 5%](#)




TE Part # 2176324-1
[SMV 3W 100K 5%](#)



TE Part # 2-2176323-5
[SMV 2W 10M 5%](#)



TE Part # 2176323-9
[SMV 2W 470K 5%](#)



TE Part # 2176322-5
[SMV 1W 220K 5%](#)

Customers Also Bought




TE Part #2318044-1
[CABLE ASSEMBLY, EB, SK5 POS EP 2P5](#)



TE Part #350789-1
[03P UMNL PIN HDR ASSY 94VO](#)



TE Part #1-1879502-4
[CRGH2512 5% 47K 2W](#)



TE Part #1744418-5
[5 POS EP 2.5 HDR, GLOW WIRE](#)



TE Part #292207-7
[MINI CT SGL DIP V 7P NAT](#)



TE Part #2318043-2
[CABLE ASSEMBLY, EB, 3 POS MINICT](#)




TE Part #5-2176327-3
[CRGP 0805 220K 1%](#)



TE Part #2382635-1
[LUMAWISE POWER INPUT TERMINAL BLOCK \(TB\)](#)



TE Part #292207-3
[MINI CT SGL DIP V 3P NAT](#)



TE Part #61968-1
[110 FASTON TAB TPBR](#)

Documents



Product Drawings

SMV 1W 2M7 5%

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2176322-8_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2176322-8_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2176322-8_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Metal glaze High Voltage SMD Resistor Type SMV series

English