

Combination Hammer XGT®

HR009G

40Vmax • SDS-PLUS • 30 mm • 3,9 J

Three-mode, anti-vibration rotary hammer with Quick Change Drill Chuck for professionals.

HR009G is a XGT® Battery Powered powerful Combination Hammer with low vibration due to 2 Counterweights, Anti-vibration rear handle and Anti-vibration side grip yet maintaining high power. Remote dust extraction start for professionals.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 840 min ⁻¹
Impacts per Minute (IPM)	0 - 4500 min ⁻¹
Max. Drilling Diameter in Wood	32 mm
Max. Drilling Diameter in Concrete	30 mm
Max. Drilling Diameter in Steel	13 mm
Optimum Drilling Diameter Range in Concrete	8 - 22 mm
Impact Energy	3,9 J
Drilling diameter with TCT core bit	80 mm
Electronic brake	✓
AWS ready	✓
Sound Power Level (L _{WA})	103 dB(A)

User benefits

- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Soft grip handle provides increased comfort on the job
- 3-Mode operation for "Rotation Only", "Hammering with Rotation" or "Hammering Only" for multiple applications
- Low power consumption thanks to brushless motor
- Constant speed control maintains constant speed under load

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing