



Save as PDF



Flashlights for industry 2220



The VB3 2220 LED has dual super bright white LEDs that may never need replacing and provide over 100 hours of battery burn time. Light turns on when the head is flipped up. It also pivots to a full 180° for aiming light where you need it. The built-in clip attaches to surfaces up to 1,3 cm thick. 2 CR2032 3V Lithium coin cells are included.



Materials

Body	Lens	Shroud	Switch Type
Xylex Polymer Resin	N/A	N/A	Head flips up to activate
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
Spring Loaded	Stainless Steel	Polymer	N/A

Configuration

Cat. #	Description
--------	-------------

Flashlights for industry 2220

ANSI FL1 Specifications

LIGHT SOURCE	High LED
BATTERIES	2 CR2032 Lithium (Included)
CHARGE TIME	N/A
VOLTAGE	3
LENGTH	8.9 cm (3.5")
WEIGHT W/ BATTERIES	0.09 kg (3 oz.)
WEIGHT W/O BATTERIES	0.02 kg (0.88 oz.)

LIGHT OUTPUT
RUNTIME (hours/min)
BEAM DISTANCE (meters)
PEAK BEAM INTENSITY (candela)

FL1 STANDARD	High	
	34h	
	12m	
	38cd	

Flashlights for industry 2220 Accessories

No accessories are currently available for this product

Approvals



- Listed 4S67/E184884 Class I, Div. 1
Gps. A, B, C, D, T6.

IECEx - Ex ib IIC T6 Gb IECEx ITS 10.0021