

Han 16B cover plastic/DL/HBM, HSM, HCC



Part number	09 30 016 5405
Specification	Han 16B cover plastic/DL/HBM, HSM, HCC
HARTING eCatalogue	https://b2b.harting.com/09300165405

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings Thermoplastic
Туре	Low construction High construction

Version

Locking type	Double locking lever
Size	16 B
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No



Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL	
-----------	--------	--

Commercial data

Packaging size	10
Net weight	20.52 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors