



Article number

Technical Data		
Operating current rated value	A	10
Operating voltage rated value maximum	V	230
Switching capacity active power	W	1 000
Switching capacity current	A	10
Number of switching outputs maximum		2
Suitability for use switching of C load		No
Suitability for operation Multiphase operation		No
Mounting type		Unterputz
Product extension can be installed supplementary devices		No
Product function direct operation		No
Protection class IP		IP20
Display version LED		No
Number of digital inputs		0
Bus coupling Integrated		Yes

Certificates/approvals

[Miscellaneous](#)**Further information****Gamma-TD (Tech. Documentation, ETS Product database, Invitation to tender text)**<http://www.siemens.com/gamma-td?ssn=5WG1510-2AB13>**Gamma - Catalogue**<http://www.siemens.com/gamma-catalogue>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=5WG1510-2AB13&lang=en**Industry Mall (Online ordering system)**<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=5WG1510-2AB13>

last modified:

05/19/2020