



ENGLISH

Datasheet

RS Pro NEMA L21 - 30P, 30A USA Plug, Cable Mount, 120/208 V

RS Stock No: **817-9381**



Product Details

RS Pro NEMA rated L5 - 20P twist lock main plug is used for AC main electricity in N. America and other countries. This twist lock plug has a voltage rating of 125 V ac and is current rated for 20 A. The twist-lock plug guarantees a more reliable connection, where vibration or incidental impact could disconnect a normal plug. It has screw type terminal for easy installation. The plug is suitable for industrial and commercial applications.

Features and Benefits

- Twist-Lock technology provides more reliability
- 22/30 A -125 V ac
- Insulation resistance at 500 V dc 100 Mohms per minute
- H.V. Breakdown test for 1 minute 2k V ac
- Screw termination
- Temperature range of 0 to +75 deg C
- Ideal for industrial and commercial applications
- Meets UL-498, NEMA WD 6:2003, CSA C22.2 No.42



Specifications:

Colour	Black
Connector Type	NEMA L21 - 30P
Country	USA
Current Rating	30 A
Gender	Male
Mounting Type	Cable Mount
Plug/Socket	Plug
Pole Format	3P+E
Termination Method	Quick Connect
Voltage Rating	120/208 V