

95 12 500

Cable Shears



- short design, length only 500 mm
- low weight, high leverage
- for cutting copper and aluminium single conductors as well as multiple stranded cables
- not suitable for steel wire and wire ropes
- precision ground, hardened blades
- clean and smooth cut without crushing and deformation
- low handforce required due to favourable lever ratio and special blade geometry
- guard prevents operators' fingers being pinched
- adjustable bolted joint
- cutter head: vanadium electric steel, forged, oil-hardened
- handles: aluminium tube, high-strength

Article No.	95 12 500
EAN	4003773069966
Head	burnished
Handles	with multi-component grips
Style	1
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	27
Cutting capacity copper cable, multiple-stranded mm²	150
AWG	5/0
Length mm	500
Net weight g	1090



Large cutting capacity:
max. 27 mm dia. / 150 mm²

technical change and errors excepted

