Features

- Suitable for crimping open barrel terminals
- Material: hardened steel frame with plastic grips
- Ratchet release
- Wire size range: 1.25mm² to 5.5mm²

RS PRO Crimping Tool for Barrel Terminals

RS Stock No.: 0726202



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description


RS PRO hand crimping tool for crimping barrel terminals onto wire. This ratchet hand tool has 3 crimping cavities; 1.25mm^2 (22-16 AWG), 2mm^2 (16-14 AWG) and 5.5mm^2 (12-10 AWG). This RS Pro crimp tool has been designed for professional use with the highest attention to details.

General Specifications

Crimp Tool Type	Plier
Crimp Connector Type	barrel terminals
Crimp Profile	Open Barrel Crimp / F-Crimp
For Use With	barrel terminals
Adjustable Ratchet	Yes
No. of Crimping Positions	3

Mechanical Specifications

Dimensions	260x72 x17mm
Overall Length	260mm
Width	72mm
Height	17mm
Wire Size (mm²)	1.25 mm² to 5.5mm²
Wire Size (AWG)	22 to 10 AWG
Crimp nest	1.25 mm² (22-16 AWG), 2 mm² (16-14 AWG) and 5.5 mm² (12-10 AWG)
Standard Die Length	35mm
Standard Die width	34mm
Standard Die Height	9.1mm


72 ±2
17 ±2
260 ±2

