



GaN Chargers - Retractable Cable (US plug & EU/UK Adapter)

PN: 32217

Description

- Supports charging of up to 3 devices simultaneously with a maximum total output of up to 65W.
- Equipped with 1 x USB-C® PD 3.0 up to 65W, 1 x USB-C Retractable Cable PD 3.0 up to 65W, 1 x USB-A QC 3.0 up to 60W. It provides a stable and effective charging solution for the laptop and smartphone users.
- Integrated GaN technology provides efficient charging and generates less heat.
- Support super-fast charging with USB Power Delivery 3.0, PPS, and Quick Charge 3.0 & 4+.
- Programmable Power Supply (PPS) technology delivers the right amount of power needed for the ideal charge.
- Output Display keeps you informed and aware of the real-time charging wattage and fast-charge mode status.
- Great travel companion thanks to foldable US prongs, replaceable EU and UK plugs and slim, compact design
- Made with high-quality, flame-resistant polycarbonate.
- Plastic-free packaging
- 2-year limited warranty



PN: 32217

Product Specifications

- Input: 100-240 V AC 50/60 Hz 1.7 A (max.)
- Output:
- USB-C1/C2 PD 3.0 (PPS supported):
 - 5 - 11 V = 4.5 A, 5 V = 3 A, 9 V = 3 A, 12 V = 3 A, 15 V = 3 A, 20 V = 3.25 A (65 W max.) each
 - USB-A QC 3.0: 5 V = 3 A, 9 V = 3 A, 12 V = 3 A, 20 V = 3 A (60 W max.)
- Total Output: 65 W max.
- Indoor use only!



PN	# Devices	USB-C	USB-A	Max Total Output	Power Delivery	Q.C.*
32217	3	1 x 65W + Retractable Cable 65W	1 x 60W	65W	PD 3.0	4+

* QC 4+ is only supported by USB-C port ; USB-A port only supports up to QC 3.0

Pack Content

Verbatim GaNRC65-2 GaN Charger with 2
x USB-C® PD 65W / 1 x USB-A QC 3.0
EU and UK plug Adapter
Quick Start Guide

Languages

Front of pack: English (Product description also in French)
Back of pack: English, French, German, Dutch, Italian,
Spanish, Portuguese, Polish, Russian, Czech, Hungarian,
Serbian, Croatian, Traditional Chinese, Simplified Chinese,
Korean, Japanese

Quick Installation Languages

English, German + Technical support text in English, French,
German , Dutch, Italian, Spanish, Portuguese, Polish,
Russian, Czech, Hungarian, Serbian, Croatian, Traditional
Chinese, Simplified Chinese, Korean, Japanese

GaN Chargers - Retractable Cable (US plug & EU/UK Adapter)



Reorder No.	Description	Tariff Code	Barcode	EAN-128	EAN-14
32217	Verbatim GaN Charger 65W 2 Port retractable cable display US plugs with EU and UK adaptors	85366990	023942322177	(02)00023942322177(37)10(91)892 (02)00023942322177(37)20(91)892	20023942322171 50023942322172

Reorder No.	32217
Product Dimensions L x W x H	58.5 x 50 x 50 mm
Product Weight	157 g
Units per Pack	1
Pack Dimensions L x W x H	110 x 53 x 123 mm
Pack Weight	255 g
Packs per Inner Carton	10
Inner Carton Dimensions L x W x H	285 x 265 x 130 mm
Inner Carton Weight	2900 g
Packs per Outer Carton	20
Outer Carton Dimensions L x W x H	300 x 280 x 290 mm
Outer Cartons Weight	6550 g
Outer Cartons per Layer	16
Layers per Pallet	4
Packs per Pallet	1280

