

## FEATURES

- Plug type is EU
- Timer of 12 hours
- FND, LCD or LED display
- Oscillation of 80°
- 3 choices of wind mode (Normal / Natural / Sleep)
- Display room temperature

## RS PRO Tower Fan 30.13m<sup>3</sup>/min 3 speed 230 V ac with plug: Type C - European Plug

RS Stock No.: 180-2369



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO tower fan is 35in in height and helps to keep the space fresh and aids cooling. This fan has 3-speed controls that can be controlled using a remote control. It has a supply voltage ranging from 100VAC to 240VAC and power rating of 45W.

## General Specifications

<b>Fan Type</b>	Tower
<b>Air Flow</b>	30.13m³/min
<b>Number of Speeds</b>	3
<b>Material</b>	Housing In ABS, Base in PS
<b>Finish</b>	Metallic grey painting, top cover in black
<b>Adjustable Stand</b>	No
<b>Special Features</b>	Oscillating
<b>Non-Slip Base</b>	Yes
<b>Applications</b>	Commercial, Industrial, Retail, Leisure, Home

## Electrical Specifications

<b>Power Source</b>	Mains powered
<b>Supply Voltage</b>	240VAC
<b>Plug Type</b>	Type C –European plug
<b>Power Consumption</b>	45W
<b>Noise Level</b>	57dB

## Mechanical Specifications

<b>Dimensions</b>	89cmx 31cmx 31cm
<b>Height</b>	35in

## Approvals

### Compliance/Certifications

CE / GS Approved

RS Article	Global Description
1802368	35" tower fan w/remote control 45W BS
1802369	35" tower fan w/remote control 45W EU