

## Features

- Ultra-flexible in low temperature environments
- Exceptional abrasion resistance
- Resistant to a wide range of chemicals
- Compliant with F&DA regulations
- Excellent clarity for clear visibility
- High levels of kink resistance and good memory
- 85 Shore A hardness
- Service Temperature -40°C to + 65°C

## RS PRO Hose Pipe, PUR, 10mm ID, 15.75mm OD, Clear, 25m

RS Stock No.: 339-6304



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

*This polyurethane hose features outstanding elasticity helping to provide excellent flexibility as well as having a high kink-resistance. Even in cold conditions, the reliable hose constriction remains durable, flexible and still highly kink-resistant. Resistant to a wide range of chemicals, the abrasion resistant clear hose provides excellent visibility to see blockages or issues within the hose.*

## General Specifications

Hose Pipe / Flexible Tube	Hose Pipe
Colour	Clear

## Mechanical Specifications

Inner Diameter	10mm
Outer Diameter	15.75mm
Material	PUR
Hose Pipe Action	Transfer
Maximum Working Pressure	10bar
Suitable Application	Fuel & Oil
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	+65°C
Length	25m
Reinforced	Yes
Bend Radius	95mm

## Approvals

---

Standards Met	ISO7751(1997)
---------------	---------------

---

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories