



mecalectro

## Industrial Solenoid – 8.23D.80.64



**Stroke:** 15 mm

**Force at beginning of stroke (FM: 100/25/5%):**  
18/46/115 N

**Force at end of stroke (FM: 100/25/5%):**  
80/170/290 N

**Power Consumption (FM: 100/25/5%):**  
23/85/400 W

**Total mass:** 600 g

**Degree of protection / Energetic class:** IP 40 / B

**Standard supplies:** 220Vac

**Possibles supplies:** From 24 to 230Vac

**Duty Cycle:** Permanent, impulsions (100 / 40 / 25 / 15 / 5 %)

**Standard:** NF C 79300

**Examples of applications:** Automation, blocking, composting, distribution, stamping, punching.