

Floor infostand with aluminum snap frame A4

Article number	479823	Sales unit quantity	1 Piece
Colour	Silver	Sales unit EAN	4005546735542
Packaging unit	1 piece	Packing weight (gross)	2003.6 G
Base EAN	4005546735542	Country of origin	CN



Logos and awards



Product description

- Quickly assembled information stand with robust DIN A4 aluminium folding frame, silver anodised
- High stability can be ensured by optionally filling the base (diameter: 250 mm) with sand. Additional purchase item DURABLE Sand: Product code 333516. Max. weight approx. 1.1 kg
- Round base with enclosed rubber ring prevents scratches on the floor
- Height adjustable with telescopic rod (can be adjusted in steps from 770 mm to a maximum height of 1,205 mm in portrait format)
- Folding frame can be easily rotated from portrait to landscape format
- Reading angle adjustable by ball-and-socket joint
- Low-reflection, UV-resistant protective cover
- Impact-resistant polystyrene back panel
- Mitred corners
- Ideal for restaurants, retail, museums, exhibitions, trade fairs, reception and waiting areas, conference rooms etc.

Floor infostand with aluminum snap frame A4

Product features

Outer height (mm)	1205
Outer Ø (mm)	250
Filling quantity / Filling quantity for	1 Sheet
Format / Format for	A4
Orientation Format	Portrait / landscape
Brand	DURABLE
Inner display panel width (mm)	192
Inner display panel height (mm)	279
Set includes display panels	Yes
Height adjustable	Yes
Rotate / Swivel amounts	360°
Adjustable reading angle	5° - 90°
Extendable	No
Opening for documents	4-sided
Tabs with blank labels included	No
Non-slip / Stable	Non-slip / stable
Includes assembly instructions	Yes
Antibacterial	No
Product features relating to documents	Anti-glare
Base / mount type	Floor stand