



Part Number : 349590340

Product Description : Mini50 Unsealed Receptacle, 3 Rows, with CPA, 34 Circuits, Polarization Option A, Black



Series Number : 34959

Status : Active

Product Category : Connector Housings

Documents & Resources

Drawings

[349590340_sd.pdf](#)

[PK-31301-538-001.pdf](#)

3D Models and Design Files

[349590340_stp.zip](#)

Specifications

[349590001-AS-CH-000.pdf](#)

[AS-34959-001-001.pdf](#)

[PS-34959-001-001.pdf](#)

[TS-34961-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Compliant per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	34959
Description	Mini50 Unsealed Receptacle, 3 Rows, with CPA, 34 Circuits, Polarization Option A, Black
Application	Automotive, Power, Wire-to-Board
Product Name	Mini50
UPC	887191704418

Physical

Circuits (maximum)	34
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	5.700/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	No

Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarization	A
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini50 Unsealed Vertical Hybrid Header, 3 Rows, 34 Circuits, Polarization Option A, Black, Tray	<u>349580340</u>
Mini50 Unsealed Vertical Hybrid Header, 3 Rows, 34 Circuits, Polarization Option A, Black, Tube	<u>349587340</u>
Mini50 Unsealed Vertical Hybrid Header, 3 Rows, 34 Circuits, Polarization Option A, Black, Tape and Reel	<u>349588340</u>
Mini50 Unsealed Right-Angle Hybrid Header, UL 94 HB, 34 Circuits, Polarization A, Black, Tube	<u>349617343</u>
Mini50 Unsealed Right-Angle Hybrid Header, UL 94 HB, 34 Circuits, Polarization A, Black, Tape and Reel	<u>349618343</u>
Mini50 Unsealed Right-Angle Hybrid Header, UL 94 HB, 34 Circuits, Polarization A, Black, Tray	<u>349610343</u>
Mini50 Unsealed Right-Angle Headers	<u>213355</u>

Use with Part(s)

Description	Part Number
CTX50 Unsealed Receptacle Terminals	<u>560023</u>

