

product type designation

product description



MV500 built-in ring light red MULTI

built-in red ring light (618 nm) incl. polarization filter for lighting and lenses

Built-in ring light MV540 red multi for MV540 devices (MLFB: 6GF3540-0CD10, -0GE10); incl. cross-polarization filter; Illuminant: LED 618 Nm, lighting distance up to 120 cm; mounting material enclosed; use with protective barrel (MLFB: 6GF3540-8AC11).

suitability for use

lighting switchable in segments

suitability for operation

for ranges of illumination up to 1.2 m and a flash duration from 20 us to 10 ms

ambient conditions

ambient temperature

- during operation
- during storage
- during transport

0 ... 50 °C

-30 ... +70 °C

-30 ... +70 °C

further information / internet links

internet link

- to website: TIA Selection Tool
- to web page: selection aid TIA Selection Tool
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Selection guide for cables and connectors
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<http://www.siemens.com/tia-selection-tool>
<https://support.industry.siemens.com/cs/ww/en/view/67384964>
<http://www.siemens.com/codereader>
<https://mall.industry.siemens.com>
<http://www.siemens.com/industry/infocenter>
<https://sie.ag/2QdlxcP>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

last modified:

11/9/2023 