

**These liquid-proof industrial gloves offer a rough finish dip that makes handling wet, slippery materials easier and safer.**

- 100% liquid proof.
- Soft stretchy knit liner.
- Excellent wet grip. Safer handling means increased productivity.
- These Neoprene liquid-proof industrial gloves are extremely comfortable to wear.



#### Industries

- Automotive
- Chemical
- Logistics
- Machinery and Equipment
- Warehousing

#### Applications

- Equipment repair & maintenance
- Warehousing of raw materials
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Cleaning furnaces, distillation pumps, valves or lines and crackers BTX process

Previously known as: Scorpio™ 08-354

### Key Features

- Cushions the hand, absorbs perspiration and prevents chafing
- Excellent wet grip. Safer handling means increased productivity
- Exceptional flexibility. Easier to manipulate, less tiring to the hand incorporating easy donning and removal
- Neoprene coating for a wide range of chemical protection
- Textured finish for better grip on wet and slippery materials
- Longer version than the 08-352 for further protection



### Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate (ZDBC)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards



### Specifications

BRAND   STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 08-354	Interlock cotton, Neoprene,	8, 9, 10	355 mm / 13.9 inches	Green	• 12 pairs in a box ,6 boxes in a carton

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.