

MP16/1 BS Grey



Products Low Voltage Products and Systems Industrial Plugs and Sockets Adaptors

Products Low Voltage Products and Systems Industrial Plugs and Sockets Modular Combination Boxes

General Information

Extended Product Type:	MP16/1 BS Grey
Product ID:	2CMA101654R1000
EAN:	7392696016544
Catalog Description:	Modular Combi Plastic, 16A, 1x3P+N+E, 250x300x160, 2x10/16A British outlets, IP44
Long Description:	Modular Combi MP16/1 BS Grey

Additional Information

Additional Information:	Cable entry,4 knock-outs at the top,suitable for 2xØ40mm and 2xØ25mm,at the bottom 3xØ47mm
Cable Cross-Section:	16 mm²
Cable Entry Position:	Cable entry,4 knock-outs at the top,suitable for 2xØ40mm and 2xØ25mm,at the bottom 3xØ47mm
Color:	Grey
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85389099
Data Sheet, Technical Information:	2CMC000019M0000
Declaration:	2CMC700005D0004
Declaration of Conformity - CE:	2CMC700005D0004
Degree of Protection:	IP44
EAN:	7392696016544
ETIM 4:	EC000379 - CEE socket outlet combination
ETIM 5:	EC000379 - CEE socket outlet combination
ETIM 6:	EC000379 - CEE socket outlet combination
Enclosure Material:	Plastic
Environmental Information:	2CMC700001D0002
Gross Weight:	2 kg
Housing Material:	Thermoplastic (PBT)
IIT Publishing Status:	Level 0 - Information enabled
Instructions and Manuals:	2CMC711001M0201
Invoice Description:	Ind.P-S_MP16/1 Grey BS
Minimum Order Quantity:	1 piece
Number of Poles:	5
Package Level 1 Gross Weight:	2 kg
Package Level 1 Height:	490 mm
Package Level 1 Length:	270 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	210 mm
Product Main Type:	MP
Product Net Weight:	2 kg
Protection Type:	Splashproof
Rated Current (I_n):	16 A
Rated Voltage (U_r):	346 ... 415 V
Selling Unit of Measure:	piece
Short Description:	Modular Combi Plastic, 16A, 1x3P+N+E, 250x300x160, 2x10/16A British outlets, IP44
Standards:	IEC 61439-1 IEC 61439-2
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour



