



ENGLISH

Datasheet

RS Pro Galvanised Steel 20mm IP40 10m

RS Stock No: **668-4758**



Product Details

RS Pro cable conduit is 10 m long with a nominal diameter of 20 mm and has galvanised steel construction. This IP40 rated conduit is perfect for high temperature continuous flexing applications requiring high mechanical protection. It is designed for commercial and industrial installations, including lighting, underfloor distribution, heating etc.

Features and Benefits

- IP40 rated
- Temperature range of -50 to +300°C
- Self coloured galvanised steel



Specifications:

Coating Material	Uncoated
Conduit Type	Flexible
IP Rating	IP40
Length	10 m
Material	Galvanised Steel
Maximum Operating Temperature	+300°C
Minimum Operating Temperature	-50°C
Nominal Diameter	20 mm
Operating Temperature Range	-50 to +300°C