

56884

Bucket, 260 mm, , Red



This durable 6 litres bucket is suitable for cleaning or storage of ingredients and food stuff. The bucket has a wide drip-free spout, sturdy stainless steel hanger, hand grip at the bottom that is raised from the base and calibrated for a variety of measuring units. The flat side prevents spillage and it has its own wall bracket, 16200 for storage.

Technical Data

Item Number	56884
Volume	6 Litre(s)
Material	Polypropylene Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	5 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	160 Pcs
Quantity Per Layer (Pallet)	40 Pcs.
Box Length	295 mm
Box Width	275 mm
Box Height	430 mm
Length	260 mm
Width	270 mm
Height	258 mm
Gross Weight	0,61 kg
Net Weight	0,55 kg
Cubik metre	0,0181 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Max. drying temperature	120 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020568848
GTIN-14 Number (Box quantity)	15705020568845
Commodity Code	39233090
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact