



Part Number : 1300390285
Product Description : DeviceNet Mini-Change Receptacle, 5 Poles, Female (Straight) with DeviceNet Thick Trunk Cable, 1/2 - 14 NPT Threads, 2.0m (6.56') Length
Series Number : 130039
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : DN5000-M020



Documents & Resources

Drawings
[1300390285_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130039
Description	DeviceNet Mini-Change Receptacle, 5 Poles, Female (Straight) with DeviceNet Thick Trunk Cable, 1/2 - 14 NPT Threads, 2.0m (6.56') Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	DeviceNet Trunk,Mini-Change
Type	Single Ended (pigtail)
UPC	78678829134

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	300V AC/DC

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	2.0m
Material - Component	Nickel-plated Zinc Die-Cast
Mounting Thread Size	1/2" - 14 NPT
Net Weight	175.330/g
Orientation	Straight

Panel Mount	Front
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Thick Standard Cable
Wire Size (AWG)	15, 18

This document was generated on Mar 27, 2025