

Datasheet

RS Pro 155 Series 3.5mm Pitch Right Angle PCB Terminal Block with Plug-In Termination, 3 WayRS Stock No: **874-5322****Specifications:**

Body Orientation	Right Angle
Colour	Green
Current Rating	8 A (UL), 10 A (IEC)
Depth	7.2 mm
Gender	Male
Material	Nylon 66
Mounting Type	PCB
Number of Contacts	3
Number of Rows	1
Pitch	3.5 mm
Termination Method	Plug In
Type	PCB Header
Voltage Rating	300 V (UL), 250 V (IEC)
Width	9.2 mm
American Wire Gauge	16 to 28 AWG



ENGLISH

Insulation Withstands Voltage	2000 V ac
Operating Temperature Range	-40 to +105°C
Insulation Resistance	500 mΩ
Flammability Rating	UL 94 V-0