

BS1.5VSC-H



Inline Splice max 1.5SQMM



General Information

Extended Product Type	BS1.5VSC-H
Product ID	7TBA301300R0148
EAN	5415022400830
Catalog Description	Inline Splice max 1.5SQMM
Long Description	Vinyl-Insulated Butt Splice, Length 26mm, Width 3.4mm, Diameter 4.3mm, Wire Range 0.5-1.5mm ² , Copper, Tin Plated, Temperature Range -30 to 75 Degrees C, 600V Max, Color Red

Ordering

EAN	5415022400830
Minimum Order Quantity	12000 piece
Customs Tariff Number	8536908585

Dimensions

Product Net Weight	0.907 g
--------------------	---------

Container Information

Package Level 1 Width	25.4 mm
Package Level 1 Height	101.6 mm
Package Level 1 Depth / Length	152.4 mm
Package Level 2 Units	9000 piece
Package Level 2 Width	152.4 mm
Package Level 2 Height	88.9 mm
Package Level 2 Depth / Length	177.8 mm
Package Level 3 Units	9000 piece
Package Level 3 Width	317.5 mm
Package Level 3 Height	203.2 mm
Package Level 3 Depth / Length	482.6 mm

Additional Information

Brand / Label	Spec-Kon
Color	Red
Material	Copper

Product Main Type	COMPRESSION TERMINALS
Product Name	Electrical Wiring Terminal
Product Type	Butt Splice
UPC	786210135502

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	BS1.5VSC-H
Instructions and Manuals	BS1.5VSC-H

Classifications

ETIM 6	EC001059 - Crimp splices for copper conductor
UNSPSC	39121449
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

