

cylindrical fuse holder 10 x 38 mm, 1-pole In: 32 A,Un AC: 690 V

Model	
product brand name	SETRON
product designation	Cylindrical fuse holder
General technical data	
number of poles	1
size of fuse link	10 x 38 mm
Supply voltage	
operating voltage	
• at AC rated value	690 V
protection class IP	IP20
Mechanical Design	
height	81 mm
width	18 mm
depth	64 mm
Net Weight	57 g
Certificates	
reference code according to IEC 81346-2	F
Approvals Certificates	
Environment	General Product Approval

[Environmental Con-
firmations](#)



Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information for data generation and storage
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/lowvoltage/catalogs>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7013-2>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/3NW7013-2>
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7013-2
CAx-Online-Generator
<https://www.siemens.com/cax>
Tender specifications
<https://www.siemens.com/specifications>
Characteristic curves
https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP='HAUPT'></mmp_prod_no>

last modified: 12/11/2025

