



DCD980L2

18V XRP Drill

- Latest generation XRP featuring NEW XR Li-Ion technology
- Tough 3 speed all metal transmission for increased runtime and longer tool life
- 22 position adjustable torque control for optimised precision when screwdriving

FEATURES

Latest generation XRP featuring NEW XR Li-Ion technology
Tough 3 speed all metal transmission for increased runtime and longer tool life
22 position adjustable torque control for optimised precision when screwdriving
13 mm ratcheting keyless chuck with automatic spindle lock for fast bit changes
Efficient intelligent trigger allowing total control over all applications
Bright white LED with delay feature for improved visibility and flashlight functionality
Improved grip design providing greater application control and maximum comfort
Steel belt clip and tough magnetic bit holder ensure strong storage solutions
Multi voltage charger for use with 18V, 14.4V and 10.8V XR Li-Ion slide pack batteries
Part of the intelligent XR Lithium Ion Series designed for efficiency and making applications faster

STANDARD

55 minute chargerr
2 slide pack batteries
Multi position side handle
Heavy duty carry case

SPECIFICATIONS

Voltage	18 V
Battery	3.0
Chuck Capacity	1.5-13 mm
Power Output	500 Watts
No Load Speed	0-575/0-1350/0-2000 rpm
Max. Torque	80 Nm
Max. Drilling Capacity [Wood]	50 mm
Max. Drilling Capacity [Metal]	13 mm
Weight	2.4 kg
Length	238 mm
Height	250 mm