

PRODUCT PROPERTIES						ORDERING INFORMATION					
Diameter (D) mm	Working length mm	Total length mm	Diameter (D) Inch	Shank diameter (d) mm	Shank diameter (d) Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number	
4.5	47	80	-	-	-	P1h	10	1	3165140521185	2 608 585 883	
4.8	52	86	-	-	-	P1h	10	1	3165140521192	2 608 585 884	
5	52	86	-	-	-	P1h	10	1	3165140521208	2 608 585 885	
5.1	52	86	-	-	-	P1h	10	1	3165140521215	2 608 585 886	
5.2	52	86	-	-	-	P1h	10	1	3165140521222	2 608 585 887	
5.5	57	93	-	-	-	P1h	10	1	3165140521239	2 608 585 888	
6	57	93	-	-	-	P1h	10	1	3165140521246	2 608 585 889	
6.5	63	101	-	-	-	P1h	10	1	3165140521253	2 608 585 890	
6.8	69	109	-	-	-	P1h	10	1	3165140521260	2 608 585 891	
7	69	109	-	-	-	P1h	10	1	3165140521277	2 608 585 892	
7.5	69	109	-	-	-	P1h	10	1	3165140521284	2 608 585 893	
Pack of 5											
8	75	117	-	-	-	P1h	5	1	3165140521291	2 608 585 894	
8.5	75	117	-	-	-	P1h	5	1	3165140521307	2 608 585 895	
9	81	125	-	-	-	P1h	5	1	3165140521314	2 608 585 896	
9.5	81	125	-	-	-	P1h	5	1	3165140521321	2 608 585 897	
10	87	133	-	-	-	P1h	5	1	3165140521338	2 608 585 898	
Pack of 5 Reduced shank to 10 mm											
10.2	87	133	-	-	-	P1h	5	1	3165140521345	2 608 585 899	
10.5	87	133	-	-	-	P1h	5	1	3165140521352	2 608 585 900	
11	94	142	-	-	-	P1h	5	1	3165140521369	2 608 585 901	
11.5	94	142	-	-	-	P1h	5	1	3165140521376	2 608 585 902	
12	101	151	-	-	-	P1h	5	1	3165140521383	2 608 585 903	
12.5	101	151	-	-	-	P1h	5	1	3165140521390	2 608 585 904	
13	101	151	-	-	-	P1h	5	1	3165140521406	2 608 585 905	