



## PW3 WORK TROUSERS

### DESCRIPTION

The PW3 Work Trousers with its smooth lines and stylish cut offers superb working comfort. It offers an impressive range of pockets including double rule pocket and pre-shaped, top loading knee pad pockets. Premium features incorporate crotch gusset, hammer loop and reinforced panels for extra durability. With adjustable leg length for added convenience the Urban Trousers is the smart choice for the modern workplace.

### COMPOSITION

- Titanmill Plus: 65% Polyester, 35% Cotton, 300g
- 100% Polyester 600D Fabric, 210g
- Navy/Black 28-48

### FEATURES

- Durable polycotton fabric for high performance and maximum wearer comfort
- Reflective piping for increased visibility
- Gripper elasticated inner waistline helping keep upper body garments in place
- Top-loading knee pad pockets for quick and easy access
- Free pair of kneepads included with this trousers
- 10 pockets for ample storage
- 2 Side pockets
- 2 back pockets with one open and one featuring a flap
- 1 Rule pocket
- 1 Spanner pocket
- 1 Pen pocket
- 1 Cargo pocket

### STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

### COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
T601NBR	NAVY/BLACK	28-14

### FEATURES

**HALF ELASTICATED WAIST**  
Half elasticated waist for a secure and comfortable fit

**MACHINE WASHABLE AT 60°C**  
Reusable and machine washable at 60 degrees

**UPF 40+**  
40+ UPF rated fabric to block 98% of UV rays



**PERFORMANCE WORKWEAR**

PW3™ contemporary workwear blends sports and lifestyle trends with function, a modern fit and improved comfort.

**GET THE COLLECTION**



**TECHINCAL INFORMATION**



**OEKO-TEX certification**  
13.HCN.29764

- Wash garment inside out
- Wash garment inside out and fully fastened
- Wash with similar colours
- Wash dark colours separately

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m <sup>3</sup> )	EAN13	GTIN/DUN14
T601NBR28	Navy/Black	65	45	36	.870	5850.000	5036108310500	15036108799067
T601NBR30	Navy/Black	65	45	36	.881	5850.000	5036108310517	15036108799074
T601NBR32	Navy/Black	65	45	36	.968	5850.000	5036108310524	15036108799081
T601NBR33	Navy/Black	65	45	36	.910	5850.000	5036108310531	15036108799098
T601NBR34	Navy/Black	65	45	36	.921	5850.000	5036108310548	15036108799104
T601NBR36	Navy/Black	65	45	36	.935	5850.000	5036108310555	15036108799111
T601NBR38	Navy/Black	65	45	36	1.030	5850.000	5036108310562	15036108799128
T601NBR40	Navy/Black	65	45	36	.975	5850.000	5036108310579	15036108799135
T601NBR41	Navy/Black	65	45	36	.985	5850.000	5036108310586	15036108799142
T601NBR42	Navy/Black	65	45	36	.994	5850.000	5036108310593	15036108799159
T601NBR44	Navy/Black	65	45	36	1.000	5850.000	5036108310609	15036108799166
T601NBR46	Navy/Black	65	45	36	1.020	5850.000	5036108310616	15036108799173
T601NBR48	Navy/Black	65	45	36	1.100	5850.000	5036108310623	15036108799180