



**fitted with**

**work equipment**

**connected load**

**glare-free**

**system of protection**

**class of protection**

**usage**

**luminaire body**

material

colour

**tubular sections**

material

surface

colour

**balance of articulation joints**

**weight (net)**

**mains lead**

**fastening**

1 x compact fluorescent lamp TC-LEL 18W/840 2G11  
light colour neutral white, 4000 K, Color Rendering Index (CRI)=82

Energy efficiency category B

conventional ballast

Energy efficiency index (EEI): B1

230 V/ 50 Hz

aluminiumised parabolic louvre

IP 20

I

switch

plastic

light grey

steel tube

painted

light grey

spring

approx. 3.3 kg

approx. 1.5 m; mains plug

CEE 7/VII

screw-down flange, table base (accessory), table clamp (accessory), wall bracket (accessory)



CEE 7/VII

**illuminance**

measuring conditions: d=50cm

E<sub>min</sub>: 85 lx  
E<sub>m</sub>: 415 lx  
E<sub>max</sub>: 946 lx

