

Features

- Spray adjustable from a fine spray to a concentrated jet
- Tough
- Highly Efficient
- White cover also available in Blue
- FDA approved FKM Seals
- High resistance to animal fats

RS PRO Family Name

RS Stock No.: 0458666



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Features:

- Spray adjustable from a fine spray to a concentrated jet
- Tough
- Highly Efficient
- White cover also available in Blue
- FDA approved FKM Seals
- High resistance to animal fats

Applications:

Food Processing Plants, Pharmaceutical, Chemical Processing, Abattoirs, Garages, Factories

General Specifications

Threaded Connection	Female
Thread Size	½"
Thread Standard	BSP

Mechanical Specifications

Maximum Working Pressure	24 Bar
Minimum Working Pressure	NA
Maximum Operating Temperature	95 degrees°C
Capacity l/min	74L/min
Materials:	Rubber Parts: EPDM Housing: 316 Stainless Steel Trigger: 304 Stainless Steel Pusher: 304 Stainless Steel O-ring: FDA approved FKM Gasket: NA
Dimensions	L 180mm H 160mm W 60mm
Net Weight	0.813kg

Approvals

Standards Met	FDA approved FKM Seals
---------------	------------------------