







Accessory circuit breaker 3WA, Option Plug LSIG GFs 315 A, UL listed, Basic protective function LT, ST, INST, GF, Rated current 315 A (Ground fault protection with standard setting range)



Model			
product brand name	SENTRON		
Net Weight	7 g		
Approvals Certificates			
General Product Approval	EMV	Test Certificates	
  Confirmation  	Type Test Certificates/Test Report		
Test Certificates	Maritime application	other	
Special Test Certificate	Miscellaneous 	Confirmation	
Further information			

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
 Information for data generation and storage
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
 Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/lowvoltage/catalogs>
 Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3WA9111-1EG03>
 Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/3WA9111-1EG03>
 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3WA9111-1EG03
 CAx-Online-Generator
<https://www.siemens.com/cax>
 Tender specifications
<https://www.siemens.com/specifications>
 Characteristic curves
[https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP=)



last modified:

10/18/2025 

