


## FEATURES

- **Non-Dimmable:** Ensures consistent light output without flickering
- **8.33 A Driver Current:** Supports high power LED configurations
- **176-264 V AC Input Voltage:** Compatible with a wide range of power sources
- **IP67 Rating:** Offers protection against dust and water, suitable for outdoor use
- **Constant Voltage Operation:** Provides stable voltage output for optimal LED performance
- **Single Output:** Simplifies installation and reduces wiring complexity
- **100 W Maximum Output Power:** Capable of powering multiple LED units

## RS PRO 100W LED Driver, 12V Constant Voltage

RS Stock No: 642-780



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO 100W LED Driver is designed to provide reliable power to LED lighting systems. With a constant voltage output of 12V, this driver is ideal for applications requiring stable and efficient power delivery. Its robust design ensures durability and performance in various environments.

### General Specifications

Dimming Operation	Non-Dimmable
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

### Electrical Specifications

Driver Current	8.33 A
Input Voltage	176-264 V ac
Input Voltage Type	AC
Maximum Output Power	100 W
Output Voltage	12 V

### Protection Category

IP Rating	IP67
-----------	------

### Approvals

Standards/Approvals	CE, EEN 55015, EN 61000-3-2, EN 61000-3-3, EN 61547, EN61000-4-2,3,4,5,6,8,11, EN61347-1, EN61347-2-13
---------------------	--