

98  
6

**Insulating Mats** from rubber

DIN VDE 0680-1



98 67 05

1000V

- for added protection when working live or close to live parts

Article No.	EAN 4003773-		Dimensions mm	Thickness mm	g
98 67 05	026600	1000V	500 x 500	1.0	301
98 67 10	026617		1000 x 1000	1.0	1200

98  
90

**PUK® Junior Hacksaw**

IEC 60900 DIN EN 60900



98 90

1000V

- saw blade for metal and wood with 25 teeth per inch, exchangeable

Article No.	EAN 4003773-	mm		Saw blade length mm	g
98 90	028321	240	1000V	150	174

98  
9

**Compact Tool Case** 17 parts

with insulated tools for works on electrical installations

IEC 60900 DIN EN 60900

- shock-resistant plastic case
- containing a range of insulated KNIPEX tools for works on electrical installations
- foam inserts with recesses for the tools
- fixable partition wall
- dimensions, exterior (W x H x D): 360 x 110 x 310 mm



98 99 11

1000V

Article No.	EAN 4003773-		Units		g
98 99 11	026624	Compact Tool Case 17 parts			3675
		03 07 200 Combination Pliers	1	1000V	
		70 07 160 Diagonal Cutter	1	1000V	
		98 20 35 Screwdrivers for slotted screws	1		
		98 20 40	1	1000V	
		98 20 55	1		
		98 24 00 Screwdrivers for cross-recessed screws	1	1000V	
		98 42 Reversible Ratchet	1	1000V	
		98 45 125 Extension Bars	1	1000V	
		98 45 250	1		
		98 47 10	1		
		98 47 11	1		
		98 47 12	1		
		98 47 13 Hexagon Sockets for hexagonal screws	1	1000V	
		98 47 14	1		
		98 47 17	1		
		98 47 19	1		
		98 52 Cable Knife	1	1000V	