

## Han 16HPR EasyCon PE Modular Frame a-f



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 016 9934
Specification	Han 16HPR EasyCon PE Modular Frame a-f
HARTING eCatalogue	<a href="https://harting.com/09400169934">https://harting.com/09400169934</a>

### Identification

Category	Accessories
Type of accessory	Frame
Description of the accessory	for up to 6 single modules a ... f

### Version

Size	16 B
Pack contents	1x male PE adapter 1x female PE adapter 2x M4/M5 distance bolts (AF 7) 2x M5/M6 distance bolts (AF 7) 2x M3 screw 2x M4 screw 2x washer SK S4

### Technical characteristics

Conductor cross-section	4 ... 10 mm <sup>2</sup> PE terminal power side 1 ... 2.5 mm <sup>2</sup> PE terminal signal side
Tightening torque	0.5 Nm Fixing screws M3 1.5 Nm Fixing screws M4 6 Nm Distance bolt 0.8 Nm PE terminal clamp 1 ... 2.5 mm <sup>2</sup> 1.5 Nm PE terminal clamp 4 ... 10 mm <sup>2</sup>
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



**Pushing Performance**  
Since 1945

## Material properties

Material (accessories)	Zinc die-cast
	Stainless steel

## Commercial data

Packaging size	1
Net weight	252 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140194427
eCl@ss	27440210 Fixing element for industrial connectors
ETIM	EC002310
UNSPSC 24.0	39121466