



Figure similar

Surge suppressor RC element for snapping on 24-48 V AC / 24-70 V DC for contactors Size 8-12, AC operation Size 3-6, DC operation

product category	Surge suppressor		
product designation	RC element		
product type designation	3TX7		
General technical data			
certificate of suitability	CE / UL / CSA		
Substance Prohibittance (Date)	07/01/2006		
Net Weight	0.09 kg		
type of voltage of the control supply voltage	AC/DC		
control supply voltage at AC			
• at 50 Hz rated value			
• at 60 Hz rated value	24 ... 48 V		
control supply voltage frequency			
• 1 rated value			
• 2 rated value	60 Hz		
control supply voltage at DC rated value	24 ... 70 V		
design of the surge suppressor	RC element		
Ambient conditions			
ambient temperature			
• during operation			
• during storage	-40 ... +80 °C		
Approvals Certificates			
General Product Approval		other	Environment



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information for data generation and storage
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3TX7522-3R>
Cax online generator
<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TX7522-3R>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/3TX7522-3R>

last modified:

4/2/2025 