

Datasheet

RS Pro 7 Digit, Digital, Counter, 10Hz, 24 V dc

RS Stock No: **896-7043**



Product Details

RS Pro counter with 7 digit display, has frequency of 10 Hz and supply voltage of 24 V dc. This electromechanical impulse counter is compact in size, making them ideal where space is limited and are suitable for panel mounting. The digital counter with 53.45 mm depth, is suitable for applications such as machine tools, business machines, test instruments, amusement instruments and measuring devices.

Features and Benefits

- 7-digit (3.6 mm), non-resettable
- Compact size and robust design
- Panel mount
- High degree of accuracy and reliability
- Wide temperature range
- Supply voltage of 12 V dc or 24 V dc (depending on model)
- Shock and vibration proof

**Specifications:**

| | |
|-------------------------------|-----------------------------|
| Approvals | RoHS Compliant; CE; NEMA 4X |
| Count Mode | Pulse |
| Function | Impulse Counter |
| Meter Type | Electronic |
| Cutout Height | 24.1 mm |
| Cutout Width | 36.8 mm |
| Depth | 53.45 mm |
| Maximum Count Frequency | 10 Hz |
| Maximum Operating Temperature | +50°C |
| Maximum Temperature | +50°C |
| Measurement Range | 0 to 9999999 |
| Minimum Measurement | 0 |
| Minimum Operating Temperature | -5°C |
| Number of Digits | 7 |
| Connection Type | Screw |
| Cutout Size | 36.8 x 24.1 mm |
| Digit Height | 3.6 mm |
| Display Range | 0 to 9999999 |
| Display Type | Digital |
| Input Type | Voltage |
| Mounting Type | Panel Mount |
| Reset Method | No Reset |
| Supply Voltage | 24 V dc |