

Metalfilm Resistors

CBR-11

(2 Flap FL24/10) 48 Values / 1.850 Pieces

Type/Brand: MBA 0204-50 (1,6ø x 3,6mm) / Vishay Beyschlag

Wattage: 0,4W at +70°C

Value Range: 10Ω-1MΩ (E6/E12)

Tolerance: ±1%

TC: 50ppm/°C

Values-Quantities Selection:

10	50x	15	25x	22	25x	33	25x	47	25x	68	25x
100	50x	150	50x	180	25x	220	50x	270	25x	330	50x
390	25x	470	50x	560	25x	680	50x	820	25x	1K0	50x
1K2	25x	1K5	50x	1K8	25x	2K2	50x	2K7	25x	3K3	50x
3K9	25x	4K7	50x	5K6	25x	6K8	50x	8K2	25x	10K	50x
12K	25x	15K	50x	18K	25x	22K	50x	27K	25x	33K	50x
39K	25x	47K	50x	56K	25x	68K	50x	82K	25x	100K	50x
150K	50x	220K	50x	330K	50x	470K	50x	680K	50x	1M0	50x

CBR-12

(2 Flap FL24/10) 48 Values / 1.480 Pieces

Type/Brand: MBB 0207-50 (2,5ø x 6,3mm) / Vishay Beyschlag

Wattage: 0,6W at +70°C

Value Range: 10Ω-1MΩ (E6/E12)

Tolerance: ±1%

TC: 50ppm/°C

Values-Quantities Selection:

10	40x	15	20x	22	20x	33	20x	47	20x	68	20x
100	40x	150	40x	180	20x	220	40x	270	20x	330	40x
390	20x	470	40x	560	20x	680	40x	820	20x	1K0	40x
1K2	20x	1K5	40x	1K8	20x	2K2	40x	2K7	20x	3K3	40x
3K9	20x	4K7	40x	5K6	20x	6K8	40x	8K2	20x	10K	40x
12K	20x	15K	40x	18K	20x	22K	40x	27K	20x	33K	40x
39K	20x	47K	40x	56K	20x	68K	40x	82K	20x	100K	40x
150K	40x	220K	40x	330K	40x	470K	40x	680K	40x	1M0	40x

CBR-13