



ENGLISH

Datasheet

Stock No: 368-0227

RS Pro PET, PVC transparent Flexible Tube 25m Long Reinforced, 100mm Bend Radius, Applications Various



Product Details

RS Standard Clear Reinforced PVC Hose

Minimised longitudinal movement under pressure

Reinforced with high tensile polyester fibres

Note

Working Pressure is at +23°C

PVC Industrial Hoses - Clear

A range of industrial hoses made from Cadmium free materials. Offering excellent abrasion resistance and good flexibility, they are Silicone free with a service temperature of -15°C to +60°C.

Specifications:

Inner Diameter	16mm
Outer Diameter	22mm
Material	PET, PVC
Colour	Transparent
Reinforced	Yes
Suitable Applications	Compressed Air, Food, Water
Length	25m
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+60°C
Maximum Working Pressure	10 bar
Bend Radius	100mm
Operating Temperature Range	-15 to +60 °C