

PREVOST FILTRATION - SINGLE UNITS

Filter



Part number	Female thread	Flow rate at 6.00 bar (l/min) ($\Delta P = 0.30$ bar)	Temperature min/ max (°C)	Max. operating pressure (bar)	Filtration (μm)	Net weight (Kg)
ATU F25100	G1/8	700.00	5.00 / 50.00	10.00	25.00	0,323
ATU F25101	G1/4	950.00	5.00 / 50.00	10.00	25.00	0,323
ATU F25103	G1/2	3300.00	5.00 / 50.00	10.00	25.00	0,65

