



professionalLINE Cable Reel RN IP44 50m H07RN-F 3G1,5

Basic data:

Product number: 9201500100
EAN: 4007123637508
Article type: KA 5100

Product information:



- Pro-reel with rollover protection on all sides.
- Stable on all four sides, perfect cable management from all four sides.
- Large, sturdy fold-down turning handle rolls cables in and out effortlessly.
- Sturdy carrying handles and plug storage compartments on all four sides.
- The body and reel are made of Rubbabren, an extremely shock- and impact-resistant plastic and rubber mix. For permanent use in toughest conditions.
- Cold-resistant to -25 °C.
- RN cable is very robust, oil resistant and especially suited for professional use and on site.
- 4 water-jet protected earthed socket outlets with self-closing protective caps.
- With extra robust earthed plug.
- Thermal cut-out protection, indicator shows overheating or overloading.
- With visual readiness indicator in the socket insert.

Productline's value propositions:

Cable: H07RN-F 3G1,5

Cable colour: black

Colour: black, orange, grey

Cable diameter: 1.5 mm²

Cable length: 50m

Max. current carrying capacity – e: 16 A

Cable quality: Rubber-Neoprene

Degree of protection (IP): IP44

Number of sockets: 4

