

SnapLock hood/
SnapLock Haube

Cable/
Kabel

D-SUB Male 15pos./
D-SUB Stift 15pol.

Mounting material
for SnapLock/
Montagematerial
für SnapLock

**Materials SnapLock hood/
Werkstoffe SnapLock Haube:**

Hood/ Haube:	ABS UL 94 V-0, Ni
Blanking plug/ Blindstopfen:	ABS UL 94 V-0, Ni
Cable strain relief/ Zugentlastung:	Steel, Ni
Clip/ Clip:	Stainless Steel/ Edelstahl
Countersunk-head screw/ Linsenkopfschraube:	Steel, Ni
Mounting material/ Montagematerial:	Steel, Ni

**Materials D-SUB Male 15pos./
Werkstoffe D-SUB Stift 15pol.:**

Insulator/ Isolierkörper:	PA 66 GF UL 94 V-0
Shell/ Gehäuse:	Steel, Sn over Ni
Crimp contact/ Crimpkontakt:	Copper alloy, Au over Ni

**Contact assignment/
Kontaktbelegung:**

D-Sub

1	black/schwarz
2	brown/braun
3	red/rot
4	pink/rosa
5	yellow/gelb
6	green/grün
7	blue/blau
8	violet/violett
9	grey/grau
10	white/weiss
11	grey pink/grau rosa
12	red blue/rot blau
13	white green/weiss grün
14	brown green/braun grün
15	white yellow/weiss gelb

Shielding
cable strain relief/
Schirmauflage
Zugentlastung

Part no/ Art.-Nr.:	Length L/ Länge L:	Cable/ Kabel:
16-512390	1,8 m	PVC, grey/grau, 15x0,34 mm ² , LiYCY Cable/Kabel: 781-GN31500
16-512400	3 m	
16-512410	5 m	

tolerance of cable/ <i>Kabeltoleranz:</i>		L <= 4 m: L + 40 mm L > 4 m: L + 1 %		 dim. in mm		D-Sub Male 15pol. in SnapLock hood with cable and mounting material <i>D-SUB Stift 15pol. in SnapLock Haube mit Kabel und Befestigungsmaterial</i>					
general tolerance/ <i>Allgemeintoleranz:</i>		0 ± 0,50 mm 0,0 ± 0,25 mm 0,00 ± 0,10 mm ° ± 5°		<table><tr><td>Date/<i>Datum</i></td><td>Name</td></tr><tr><td>drawn/ <i>gez.</i> 26.11.2024</td><td>Lehmenkühler</td></tr><tr><td>appd./ <i>gepr.</i> 02.12.2024</td><td>Koch</td></tr></table>						Date/ <i>Datum</i>	Name
Date/ <i>Datum</i>	Name										
drawn/ <i>gez.</i> 26.11.2024	Lehmenkühler										
appd./ <i>gepr.</i> 02.12.2024	Koch										
Index: b 09.04.2025 JLE		scale/ <i>Maßstab:</i> 2:1				dwg no / Z.-nr.: 16K1A4395		DIN- A3			
						Customer specific product		1 / 1			