

SITRANS FM MAG 6000i Electromagnetic flow transmitter, works with sensors of type MAG 1100, MAG 3100 and MAG 5100W. Suitable for volume flow measurement of liquids (conductive), die-cast aluminium enclosure. . Remote transmitter Die cast aluminium Processing code Standard transmitter: 18-90 V DC, 115-220 V AC 50/60 Hz Standard sensor: FM Class I, Div 2, CSA Class I,Div 2 Local Display No Communication . Metric

Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)

<https://support.industry.siemens.com/cs/products?mf=ps&lc=en-WW>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>

