



Outlet filter, Extract: W: 125 mm, H: 125 mm, RAL 7035, IP55

Model		
product brand name		SIVACON
product designation		outlet filter
type of ventilation		ventilation
fan design withdrawable fan		No
design of the product EMC version		No
General technical data		
cutout width		125 mm
cutout height		125 mm
Protection class		
protection class IP		IP55
Appearance		
color		light grey
Product details		
product component fan		No
Mechanical Design		
height		148 mm
width		148 mm
depth		28 mm
installation location		Control cabinet...panels, door
fastening method		snap-on mounting
fastening method		
• 19-inch installation		No
• wall mounting		Yes
net weight		0.2 kg
material		plastic
ambient temperature during operation		
• minimum		-20 °C
• maximum		65 °C
Approvals Certificates		
General Product Approval		other
		Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6500-5GV25>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6500-5GV25>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6500-5GV25

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

