

## Maus

### 00053879 "Roma" Wireless Laser Mouse, noiseless, black



Highlightstext:

- Wireless 6-button mouse with very high scan precision on practically all surfaces
- The laser sensor makes exact control of the cursor possible on almost any surface
- Noiseless main buttons for relaxed working without disturbing noise
- Practical 4-way scroll wheel for vertical and horizontal scrolling
- Storable USB receiver can be transported inside the mouse to save space
- Separate on/off switch allows for energy-saving use of the mouse
- If the battery voltage is too low, the indicator light begins to flash which means that the batteries should be replaced
- With software for reprogramming the buttons
- The sensitivity can be switched to 800 and 1600 dpi
- Smart-Link technology for easy start-up

System Requirements:

- Operating system: Windows 10/8/7/Vista/XP
- USB port

Note for Consumers:

The main buttons (left and right mouse button) do not make noise. The software for reprogramming the buttons is available for free download. You will find the corresponding link in the operating instructions.

Technical Details:

- Connection: USB-A Plug
- Connection: Wireless
- Model: Standard Mouse
- Number of Mouse Buttons: 6 Buttons incl. 4-Way Scroll Wheel
- Scroll Function: 4-Way Scroll Wheel
- Sensors: Laser
- Width x Depth x Height: 7.2 x 12,3 x 4 cm
- Resolution: 1600/800 dpi
- Colour: Black

Scope Of Delivery:

- 1 "Roma" wireless laser mouse
- 1 USB receiver
- 2 AA batteries
- Operating instructions

	Brand	Item-no.	VE
	<b>hama</b> <sup>®</sup>	00053879	8