

Technical data sheet

Article number:
151-04461

MAGMB2

Product Group	Cable tie mounts
Product Family	MAGMB-Series square design, magnetic
Material	Polyamide 6.6 (PA66), Neodymium alloy R5 (NDFEBR5)
Colour	Black (BK)
CE Certification	No
Flammability	UL 94 V2 (excluding adhesive)
Height (H)	4.1 mm
Length (L)	13.0 mm
Operating Temperature	-40 °C to +85 °C
Package Content	50 pcs.
Package Content packed in	bag
ROHS compliant	Yes
Variant	Mounts
Width (W)	13.0 mm

HF ✓

RoHS ✓